

Eaton PDG23P0060B2NJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 60A, 100kA/480V, PXR10 LSI TU, Standard Line and Load (PDG2X3T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23P0060B2NJ
UPC	786679262597
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 CCC Marked UL 489

AMPERAGE RATING	60 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T281
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	200 kAIC @240V (UL)
	100 kAIC Icu/ 70 kAIC Ics/
	220 kAIC Icm @380-415V (IEC)
	200 kAIC Icu/ 150 kAIC Ics/
	440 kAIC Icm @240V (IEC)
	35/25 kAIC Icu/ 18/13 kAIC Ics @525V South Africa (IEC)
	85 kAIC Icu/ 40 kAIC Ics/
	187 kAIC Icm @480V Brazil (IEC)
	22 kAIC Icu @125 Vdc
	22 kAIC Icu @250 Vdc
NUMBER OF POLES	10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)
	35/25 kAIC @600V (UL/CSA)
	100 kAIC Icu/ 65 kAIC Ics/
	220 kAIC Icm @440V (IEC)
	100 kAIC @480V (UL)
	25 kAIC @600V (UL/CSA)
SPECIAL FEATURES	None

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

