



□□□□

## Eaton PDG23P0150E2NN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 150A, 100kA/480V, PXR20 LSI TU, No Terminals

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG23P0150E2NN
<b>UPC</b>	786679269404
<b>PRODUCT LENGTH/DEPTH</b>	88.9 mm
<b>PRODUCT HEIGHT</b>	152.4 mm
<b>PRODUCT WIDTH</b>	104.6 mm
<b>PRODUCT WEIGHT</b>	1.82 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CCC Marked IEC 60947-2 UL 489 CSA

□□□□

<b>AMPERAGE RATING</b>	150 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T283
<b>CIRCUIT BREAKER TYPE</b>	PD2 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>TERMINALS</b>	No Terminals
<b>FRAME</b>	2
<b>CLASS</b>	Class A
<b>INTERRUPT RATING</b>	100 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Electronic
<b>VOLTAGE RATING - MAX</b>	600 V

**INTERRUPT RATING RANGE**

200 kAIC @240V (UL)  
 200 kAIC Icu/ 150 kAIC Ics/  
 440 kAIC Icm @240V (IEC)  
 10 kAIC Icu/ 5 kAIC Ics/ 21  
 kAIC Icm @690V (IEC)  
 85 kAIC Icu/ 40 kAIC Ics/  
 187 kAIC Icm @480V Brazil  
 (IEC)  
 100 kAIC Icu/ 65 kAIC Ics/  
 220 kAIC Icm @440V (IEC)  
 22 kAIC Icu @125 Vdc  
 35/25 kAIC @600V  
 (UL/CSA)  
 35/25 kAIC Icu/ 18/13 kAIC  
 Ics @525V South Africa  
 (IEC)  
 100 kAIC @480V (UL)  
 22 kAIC Icu @250 Vdc  
 100 kAIC Icu/ 70 kAIC Ics/  
 220 kAIC Icm @380-415V  
 (IEC)  
 25 kAIC @600V (UL/CSA)

<b>NUMBER OF POLES</b>	Three-pole
<b>TRIP RATING</b>	150 A
<b>SPECIAL FEATURES</b>	None

□□

