



□□□□

Eaton PDG23P0150E3RL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 150A, 100kA/480V, PXR20 LSIG w/ Relays, Standard Terminals Load Only (PDG2X3TA225)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23P0150E3RL
UPC	786679848166
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CCC Marked IEC 60947-2 CSA



Powering Business Worldwide

□□□□

□□

AMPERAGE RATING	150 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T285
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Load Only
FRAME	2
CLASS	Class A
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	<p>100 kAIC Icu/ 70 kAIC Ics/ 220 kAIC Icm @380-415V (IEC)</p> <p>22 kAIC Icu @250 Vdc</p> <p>10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)</p> <p>22 kAIC Icu @125 Vdc</p> <p>85 kAIC Icu/ 40 kAIC Ics/ 187 kAIC Icm @480V Brazil (IEC)</p> <p>200 kAIC @240V (UL)</p> <p>100 kAIC Icu/ 65 kAIC Ics/ 220 kAIC Icm @440V (IEC)</p> <p>100 kAIC @480V (UL)</p> <p>200 kAIC Icu/ 150 kAIC Ics/ 440 kAIC Icm @240V (IEC)</p> <p>35/25 kAIC @600V (UL/CSA)</p> <p>35/25 kAIC Icu/ 18/13 kAIC Ics @525V South Africa (IEC)</p> <p>25 kAIC @600V (UL/CSA)</p>
NUMBER OF POLES	Three-pole
TRIP RATING	150 A
SPECIAL FEATURES	Relays

