

Eaton PDG24G0060E2CJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Four Pole (100% N), 60A, 35kA/480V, PXR20 LSI w/ CAM Link and Relays, Standard Line and Load (PDG2X4T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG24G0060E2CJ
UPC	786679299630
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	139.5 mm
PRODUCT WEIGHT	2.46 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked IEC 60947-2 UL 489 CSA

AMPERAGE RATING	60 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T283
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
COMMUNICATION	CAM Link
INTERRUPT RATING	35 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)
	10 kAIC Icu @250 Vdc
	30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)
	10 kAIC Icu @125 Vdc
	18 kAIC @600V (UL/CSA)
	65 kAIC @240V (UL)
	25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)
	36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)
	55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)
	35 kAIC @480V (UL)
INTERRUPT RATING RANGE	8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)
NUMBER OF POLES	Four-pole (100% N)
TRIP RATING	60 A
SPECIAL FEATURES	CAM / Relays

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

