



□□□□

Eaton PDG24G0225E2MK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Four Pole (100% N), 225A, 35kA/480V, PXR20 LSI w/ Modbus RTU and Relays, Standard Terminals Line Only (PDG2X4TA225)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG24G0225E2MK
UPC	786687065258
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	139.5 mm
PRODUCT WEIGHT	2.46 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked



Powering Business Worldwide

□□□□

□□

AMPERAGE RATING	225 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T283
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Terminals Line Only
FRAME	2
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	35 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	35 kAIC @480V (UL) 36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC) 10 kAIC Icu @250 Vdc 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC) 18 kAIC @600V (UL/CSA) 30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC) 55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC) 65 kAIC @240V (UL) 8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC) 10 kAIC Icu @125 Vdc 20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)
NUMBER OF POLES	Four-pole (100% N)
TRIP RATING	225 A
SPECIAL FEATURES	Modbus / relays

