

Eaton

PDG24M0150E3WN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Four Pole, 150A, 65kA/480V, PXR20 LSIG w/ Modbus RTU, ZSI and Relays, No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG24M0150E3WN
UPC	786689221676
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	139.5 mm
PRODUCT WEIGHT	2.46 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA CCC Marked IEC 60947-2 UL 489

AMPERAGE RATING	150 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T285
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
RATING	150A
SERIES	Power Defense
TERMINALS	No Terminals
FRAME	2
CLASS	Class A
COMMUNICATION	Modbus RTU
RATING PLUG	No
SHORT-CIRCUIT BREAKING CAPACITY	65 kAIC at 480 Vac
INTERRUPT RATING	65 kAIC at 480 Vac
CURRENT - MAX	150A
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	22 kAIC Icu @125 Vdc
	100 kAIC @240V (UL)
	50 kAIC Icu/ 40 kAIC Ics/
	105 kAIC Icm @440V (IEC)
	100 kAIC Icu/ 100 kAIC Ics/
	220 kAIC Icm @240V (IEC)
	22 kAIC Icu @250 Vdc
	25 kAIC Icu/ 10 kAIC Ics/
	52.5 kAIC Icm @525V
	South Africa (IEC)
	50 kAIC Icu/ 30 kAIC Ics/
	105 kAIC Icm @480V Brazil (IEC)
	70 kAIC Icu/ 53 kAIC Ics/
	154 kAIC Icm @380-415V (IEC)
	10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)
	65 kAIC @480V (UL)
	25 kAIC @600V (UL/CSA)
NUMBER OF POLES	Four-pole (100% N)
SPECIAL FEATURES	Modbus / ZSI / Relays



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

