


Eaton PDG24P0060B2NJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Four-pole (100% N), 60A, 100kA/480V, PXR10 LSI TU, Standard Line and Load (PDG2X4T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG24P0060B2NJ
UPC	786679451243
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	139.5 mm
PRODUCT WEIGHT	2.46 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked

AMPERAGE RATING	60 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T281
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	100 kAIC @480V (UL)
	100 kAIC Icu/ 65 kAIC Ics/
	220 kAIC Icm @440V (IEC)
	22 kAIC Icu @125 Vdc
	35/25 kAIC @600V (UL/CSA)
	10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)
	200 kAIC Icu/ 150 kAIC Ics/ 440 kAIC Icm @240V (IEC)
	200 kAIC @240V (UL)
	22 kAIC Icu @250 Vdc
	100 kAIC Icu/ 70 kAIC Ics/ 220 kAIC Icm @380-415V (IEC)
	35/25 kAIC Icu/ 18/13 kAIC Ics @525V South Africa (IEC)
	85 kAIC Icu/ 40 kAIC Ics/ 187 kAIC Icm @480V Brazil (IEC)
	25 kAIC @600V (UL/CSA)
NUMBER OF POLES	Four-pole (100% N)



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

