



□□□□

## Eaton PDG24P0150E3MJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Four-pole (100% N), 150A, 100kA/480V, PXR20 LSIG w/ Modbus RTU and Relays, Standard Line and Load (PDG2X4TA225)

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG24P0150E3MJ
<b>UPC</b>	786679337844
<b>PRODUCT LENGTH/DEPTH</b>	88.9 mm
<b>PRODUCT HEIGHT</b>	152.4 mm
<b>PRODUCT WIDTH</b>	139.5 mm
<b>PRODUCT WEIGHT</b>	2.46 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60947-2 CCC Marked



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	150 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T285
<b>CIRCUIT BREAKER TYPE</b>	PD2 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>PROTECTION</b>	100% neutral protection
<b>TERMINALS</b>	Standard Line and Load
<b>FRAME</b>	2
<b>CLASS</b>	Class A
<b>COMMUNICATION</b>	Modbus RTU
<b>INTERRUPT RATING</b>	100 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>VOLTAGE RATING - MAX</b>	600 V
<b>INTERRUPT RATING RANGE</b>	22 kAIC Icu @250 Vdc 10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC) 100 kAIC Icu/ 65 kAIC Ics/ 220 kAIC Icm @440V (IEC) 35/25 kAIC Icu/ 18/13 kAIC Ics @525V South Africa (IEC) 200 kAIC @240V (UL) 22 kAIC Icu @125 Vdc 85 kAIC Icu/ 40 kAIC Ics/ 187 kAIC Icm @480V Brazil (IEC) 100 kAIC @480V (UL) 100 kAIC Icu/ 70 kAIC Ics/ 220 kAIC Icm @380-415V (IEC) 200 kAIC Icu/ 150 kAIC Ics/ 440 kAIC Icm @240V (IEC) 35/25 kAIC @600V (UL/CSA) 25 kAIC @600V (UL/CSA)
<b>NUMBER OF POLES</b>	Four-pole (100% N)
<b>TRIP RATING</b>	150 A
<b>SPECIAL FEATURES</b>	Modbus / relays

□□

