



□□□□

Eaton PDG30M0250TFAL

Power Defense Globally Rated, Frame 3,
Four Pole (0% N), 250A, 65kA/480V, T-M
(Fxd-Adj) TU, Std Term Load Only
(PDG3X4TA350)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG30M0250TFAL
UPC	786679823385
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.39 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked UL 489 CSA IEC 60947-2



Powering Business Worldwide



AMPERAGE RATING	250 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T297
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	0% neutral protection
TERMINALS	Standard Terminals Load Only
FRAME	3
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	35 kAIC @600V (UL/CSA) 15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 22 kAIC Icu @250 Vdc 50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 30 kAIC Icu/ 15 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) 100 kAIC @240V (UL) 65 kAIC @480V (UL) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)
NUMBER OF POLES	Four-pole (0% N)



