



□□□□

Eaton PDG32G0250E3ZJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 250A, 35kA/480V, PXR20 LSIG w/ ZSI and Relays, Standard Line and Load (PDG3X2TA350)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG32G0250E3ZJ
UPC	786679526170
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.2163 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA CCC Marked IEC 60947-2 UL 489



Powering Business Worldwide

□□□□

AMPERAGE RATING	250 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T285
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	3
CLASS	Class A
INTERRUPT RATING	35 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE

8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)
 36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)
 20 kAIC Icu/ 7.5 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)
 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)
 30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)
 35 kAIC @480V (UL)
 18 kAIC @600V (UL/CSA)
 65 kAIC @240V (UL)
 10 kAIC Icu @250 Vdc
 55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)

NUMBER OF POLES	Two-pole
TRIP RATING	250 A
SPECIAL FEATURES	ZSI / Relays

□□

