



□□□□

Eaton PDG32K0125D5MJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 125A, 50kA/480V, PXR20D ARMS LSIG w/ Modbus RTU and Relays, Standard Line and Load (PDG3X2TA300)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG32K0125D5MJ
UPC	786679387733
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.2163 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked CSA UL 489



Powering Business Worldwide



AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T290
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	3
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	50 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	35 kAIC Icu/ 22.5 kAIC Ics/ 73.5 kAIC Icm @480V Brazil (IEC) 35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm @440V (IEC) 50 kAIC @480V (UL) 10 kAIC Icu @250 Vdc 10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC) 85 kAIC Icu/ 85 kAIC Ics/ 187 kAIC Icm @240V (IEC) 50 kAIC Icu/ 50 kAIC Ics/ 105 kAIC Icm @380-415V (IEC) 85 kAIC @240V (UL) 25 kAIC @600V (UL/CSA) 25 kAIC Icu/ 10 kAIC Ics/ 52.5 kAIC Icm @525V South Africa (IEC)
NUMBER OF POLES	Two-pole
SPECIAL FEATURES	Modbus / relays



