



□□□□

# Eaton

## PDG32M0125P2ML

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 125A, 65kA/480V, PXR25 LSI w/ Modbus RTU and Relays, Standard Terminals Load Only (PDG3X2TA300)

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG32M0125P2ML
<b>UPC</b>	786679980590
<b>PRODUCT LENGTH/DEPTH</b>	109.1 mm
<b>PRODUCT HEIGHT</b>	257.1 mm
<b>PRODUCT WIDTH</b>	138.9 mm
<b>PRODUCT WEIGHT</b>	5.2163 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL 489 CSA CCC Marked IEC 60947-2



Powering Business Worldwide



<b>AMPERAGE RATING</b>	125 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T291
<b>CIRCUIT BREAKER TYPE</b>	PD3 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>TERMINALS</b>	Standard Terminals Load Only
<b>FRAME</b>	3
<b>CLASS</b>	Class A
<b>COMMUNICATION</b>	Modbus RTU
<b>INTERRUPT RATING</b>	65 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Electronic
<b>VOLTAGE RATING - MAX</b>	600 V
<b>INTERRUPT RATING RANGE</b>	50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 35 kAIC @600V (UL/CSA) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 22 kAIC Icu @250 Vdc 30 kAIC Icu/ 15 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) 100 kAIC @240V (UL) 65 kAIC @480V (UL)
<b>NUMBER OF POLES</b>	Two-pole
<b>SPECIAL FEATURES</b>	Modbus / relays

