



□□□□

Eaton

PDG32M0250P4MK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 250A, 65kA/480V, PXR25 ARMS LSI w/ Modbus RTU and Relays, Standard Terminals Line Only (PDG3X2TA350)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG32M0250P4MK
UPC	786679989258
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.2163 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	250 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T292
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Line Only
FRAME	3
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 30 kAIC Icu/ 15 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) 100 kAIC @240V (UL) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 22 kAIC Icu @250 Vdc 35 kAIC @600V (UL/CSA) 50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 65 kAIC @480V (UL)
NUMBER OF POLES	Two-pole
SPECIAL FEATURES	Modbus / relays

□□

