

Eaton PDG32M0400E4RK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 400A, 65kA/480V, PXR20 ARMS LSI w/ Relays, Standard Terminals Line Only (PDG3X2TA400)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG32M0400E4RK
UPC	786679956809
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.2163 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CSA CCC Marked UL 489

AMPERAGE RATING	400 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T284
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Line Only
FRAME	3
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	100 kAIC @240V (UL) 22 kAIC Icu @250 Vdc
NUMBER OF POLES	Two-pole
TRIP RATING	400 A
SPECIAL FEATURES	Relays

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

