



□□□□□

## Eaton PDG32M0400P5DL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 400A, 65kA/480V, PXR25 ARMS LSIG w/ Modbus RTU, CAM Link and Relays, Standard Terminals Load Only (PDG3X2TA400)

□□□□

|                             |                                                 |
|-----------------------------|-------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Power Defense molded case circuit breaker |
| <b>CATALOG NUMBER</b>       | PDG32M0400P5DL                                  |
| <b>UPC</b>                  | 786679770276                                    |
| <b>PRODUCT LENGTH/DEPTH</b> | 109.1 mm                                        |
| <b>PRODUCT HEIGHT</b>       | 257.1 mm                                        |
| <b>PRODUCT WIDTH</b>        | 138.9 mm                                        |
| <b>PRODUCT WEIGHT</b>       | 5.2163 kg                                       |
| <b>COMPLIANCES</b>          | RoHS Compliant                                  |
| <b>CERTIFICATIONS</b>       | IEC 60947-2<br>CCC Marked<br>CSA<br>UL 489      |



Powering Business Worldwide

| □□□□                                     |                                             |
|------------------------------------------|---------------------------------------------|
| AMPERAGE RATING                          | 400 A                                       |
| VOLTAGE RATING                           | 600 Vac                                     |
| TRIP TYPE                                | T294                                        |
| CIRCUIT BREAKER TYPE                     | PD3 Global                                  |
| CIRCUIT BREAKER FRAME TYPE               | Complete breaker                            |
| TERMINALS                                | Standard Terminals Load Only                |
| FRAME                                    | 3                                           |
| CLASS                                    | Class A                                     |
| COMMUNICATION                            | Modbus RTU and CAM Link                     |
| INTERRUPT RATING                         | 65 kAIC at 480 Vac                          |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600                                         |
| SWITCH OFF TECHNIQUE                     | Electronic                                  |
| VOLTAGE RATING - MAX                     | 600 V                                       |
| INTERRUPT RATING RANGE                   | 100 kAIC @240V (UL)<br>22 kAIC Icu @250 Vdc |
| NUMBER OF POLES                          | Two-pole                                    |
| SPECIAL FEATURES                         | Modbus / Relays / CAM                       |

□□

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| □□:             |



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

