



□□□□

Eaton PDG32NH250E5RJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 250A High Override, 85kA/480V, PXR20 ARMS LSIG w/ Relays, Standard Line and Load (PDG3X2TA631)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG32NH250E5RJ
UPC	786679401422
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.2163 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING 250A High Override**VOLTAGE RATING** 600 Vac**TRIP TYPE** T286**CIRCUIT BREAKER TYPE** PD3 Global**CIRCUIT BREAKER FRAME TYPE** Complete breaker**TERMINALS** Standard Line and Load**FRAME** 3**CLASS** Class A**INTERRUPT RATING** 85 kAIC at 480 Vac**RATED OPERATION VOLTAGE (UE) AT AC - MAX** 600**SWITCH OFF TECHNIQUE** Electronic**VOLTAGE RATING - MAX** 600 V**INTERRUPT RATING RANGE**

50 kAIC @600V (UL/CSA)
 20 kAIC Icu/ 10 kAIC Ics/ 42 kAIC Icm @690V (IEC)
 22 kAIC Icu @250 Vdc
 35 kAIC Icu/ 25 kAIC Ics/ 73.5 kAIC Icm @525V South Africa (IEC)
 70 kAIC Icu/ 70 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)
 150 kAIC Icu/ 100 kAIC Ics/ 330 kAIC Icm @240V (IEC)
 150 kAIC @240V (UL)
 85 kAIC @480V (UL)
 65 kAIC Icu/ 40 kAIC Ics/ 143 kAIC Icm @480V Brazil (IEC)
 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @440V (IEC)

NUMBER OF POLES Two-pole**TRIP RATING** 250 A high override**SPECIAL FEATURES** Relays

□□

