



□□□□

Eaton PDG32P0125E2NN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 3, Two Pole, 125A, 100kA/480V, PXR20 LSI TU, No Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG32P0125E2NN
UPC	786679251522
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.2163 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CCC Marked CSA IEC 60947-2



Powering Business Worldwide

□□□□

AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T283
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	3
CLASS	Class A
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE

20 kAIC Icu/ 10 kAIC Ics/ 42 kAIC Icm @690V (IEC)
 100 kAIC @480V (UL)
 65 kAIC @600V (UL/CSA)
 85 kAIC Icu/ 40 kAIC Ics/
 187 kAIC Icm @480V Brazil (IEC)
 100 kAIC Icu/ 50 kAIC Ics/
 220 kAIC Icm @440V (IEC)
 40 kAIC Icu/ 25 kAIC Ics/ 84 kAIC Icm @525V South Africa (IEC)
 200 kAIC Icu/ 150 kAIC Ics/
 440 kAIC Icm @240V (IEC)
 22 kAIC Icu @250 Vdc
 100 kAIC Icu/ 70 kAIC Ics/
 220 kAIC Icm @380-415V (IEC)
 200 kAIC @240V (UL)

NUMBER OF POLES	Two-pole
TRIP RATING	125 A
SPECIAL FEATURES	None

□□

