



□□□□

Eaton PDG33F0125E5RL

Power Defense Globally Rated, Frame 3,
Three Pole, 125A, 25kA/480V, PXR20 ARMS
LSIG w/ Relays, Std Term Load Only
(PDG3X3TA300)

□□□□

| | |
|---------------------------------|-------------------------------------------------------|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG33F0125E5RL |
| UPC | 786679699027 |
| PRODUCT LENGTH/DEPTH | 109.1 mm |
| PRODUCT HEIGHT | 257.1 mm |
| PRODUCT WIDTH | 138.9 mm |
| PRODUCT WEIGHT | 5.92 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | CSA UL 489 CCC Marked IEC 60947-2 |



Powering Business Worldwide

□□□□

□□

| | |
|-------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| AMPERAGE RATING | 125 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T286 |
| CIRCUIT BREAKER TYPE | PD3 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| TERMINALS | Standard Terminals Load Only |
| FRAME | 3 |
| CLASS | Class A |
| INTERRUPT RATING | 25 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 18 kAIC Icu/ 5 kAIC Ics/ 37.8 kAIC Icm @525V South Africa (IEC) 10 kAIC Icu @250 Vdc 25 kAIC @480V (UL) 35 kAIC @240V (UL) 35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm @240V (IEC) 25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @380-415V (IEC) 20 kAIC Icu/ 20 kAIC Ics/ 42 kAIC Icm @480V Brazil (IEC) 14 kAIC @600V (UL/CSA) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @440V (IEC) |
| NUMBER OF POLES | Three-pole |
| TRIP RATING | 125 A |
| SPECIAL FEATURES | Relays |

