



□□□□

## Eaton PDG33G0250E4RJ

Power Defense Globally Rated, Frame 3,  
Three Pole, 250A, 35kA/480V, PXR20 ARMS  
LSI w/ Relays, Std Line Load Term  
(PDG3X3TA350)

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG33G0250E4RJ
<b>UPC</b>	786679485941
<b>PRODUCT LENGTH/DEPTH</b>	109.1 mm
<b>PRODUCT HEIGHT</b>	257.1 mm
<b>PRODUCT WIDTH</b>	138.9 mm
<b>PRODUCT WEIGHT</b>	5.92 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CCC Marked UL 489 IEC 60947-2 CSA



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	250 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T284
<b>CIRCUIT BREAKER TYPE</b>	PD3 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>TERMINALS</b>	Standard Line and Load
<b>FRAME</b>	3
<b>CLASS</b>	Class A
<b>INTERRUPT RATING</b>	35 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Electronic
<b>VOLTAGE RATING - MAX</b>	600 V

**INTERRUPT RATING RANGE**

10 kAIC Icu @250 Vdc  
8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)  
20 kAIC Icu/ 7.5 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)  
36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)  
30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)  
55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)  
65 kAIC @240V (UL)  
18 kAIC @600V (UL/CSA)  
35 kAIC @480V (UL)  
25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)

<b>NUMBER OF POLES</b>	Three-pole
<b>TRIP RATING</b>	250 A
<b>SPECIAL FEATURES</b>	Relays

□□

