



□□□□□

Eaton PDG33M0400E5XN

Power Defense Globally Rated, Frame 3,
Three Pole, 400A, 65kA/480V, PXR20 ARMS
LSIG w/ CAM Link, ZSI and Relays, No
Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG33M0400E5XN
UPC	786679517543
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.92 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA CCC Marked UL 489 IEC 60947-2

□□□□	
AMPERAGE RATING	400 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T286
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	3
CLASS	Class A
COMMUNICATION	CAM Link
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	22 kAIC Icu @250 Vdc 100 kAIC @240V (UL)
NUMBER OF POLES	Three-pole
TRIP RATING	400 A
SPECIAL FEATURES	ZSI / CAM / Relays

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

