



□□□□

Eaton

PDG34M0125E4MK

Power Defense Globally Rated, Frame 3, Four Pole, 125A, 65kA/480V, PXR20 ARMS LSI w/ Modbus RTU and Relays, Std Term Line Only (PDG3X4TA300)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG34M0125E4MK
UPC	786689227135
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.39 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA CCC Marked UL 489 IEC 60947-2



Powering Business Worldwide

□□□□

□□

AMPERAGE RATING	125 A
------------------------	-------

VOLTAGE RATING	600 Vac
-----------------------	---------

CIRCUIT BREAKER TYPE	PD3 Global
-----------------------------	------------

CIRCUIT BREAKER FRAME TYPE	Complete breaker
-----------------------------------	------------------

PROTECTION	100% neutral protection
-------------------	-------------------------

TERMINALS	Standard Terminals Line only
------------------	------------------------------

FRAME	3
--------------	---

CLASS	Class A
--------------	---------

INTERRUPT RATING	65 kAIC at 480 Vac
-------------------------	--------------------

RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
---	-----

SWITCH OFF TECHNIQUE	Electronic
-----------------------------	------------

VOLTAGE RATING - MAX	600 V
-----------------------------	-------

INTERRUPT RATING RANGE	30 kAIC Icu/ 25 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) 35 kAIC @600/347V (UL) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 65 kAIC @480/277V (UL) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 100 kAIC @240V (UL)
-------------------------------	--

NUMBER OF POLES	Four-pole
------------------------	-----------

