



□□□□

Eaton

PDG34M0250B2NK

Power Defense Globally Rated, Frame 3,
Four Pole, 250A, 65kA/480V, PXR10 LSI TU,
Std Term Line Only ()

□□□□

| | |
|-----------------------------|-------------------------------------------------|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG34M0250B2NK |
| UPC | 786689224790 |
| PRODUCT LENGTH/DEPTH | 109.1 mm |
| PRODUCT HEIGHT | 257.1 mm |
| PRODUCT WIDTH | 182.9 mm |
| PRODUCT WEIGHT | 7.39 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | IEC 60947-2 CSA CCC Marked UL 489 |



Powering Business Worldwide

□□□□

□□

| | |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| AMPERAGE RATING | 250 A |
| VOLTAGE RATING | 600 Vac |
| CIRCUIT BREAKER TYPE | PD3 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| PROTECTION | 100% neutral protection |
| TERMINALS | Standard Terminals Line only |
| FRAME | 3 |
| CLASS | Class A |
| INTERRUPT RATING | 65 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 35 kAIC @600/347V (UL) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 65 kAIC @480/277V (UL) 50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 100 kAIC @240V (UL) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 30 kAIC Icu/ 25 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) |
| NUMBER OF POLES | Four-pole |

