



□□□□□

Eaton

PDG34M0400P5MK

Power Defense Globally Rated, Frame 3,
Four Pole, 400A, 65kA/480V, PXR25 ARMS
LSIG w/ Modbus RTU and Relays, Std Term
Line Only (PDG3X4TA400)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG34M0400P5MK
UPC	786689225179
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.39 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA UL 489 IEC 60947-2 CCC Marked

□□□□

AMPERAGE RATING	400 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Terminals Line only
FRAME	3
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE

50 kAIC Icu/ 40 kAIC Ics/
105 kAIC Icm @440V (IEC)
30 kAIC Icu/ 25 kAIC Ics/ 63
kAIC Icm @525V South
Africa (IEC)
65 kAIC @480/277V (UL)
100 kAIC Icu/ 100 kAIC Ics/
220 kAIC Icm @240V (IEC)
70 kAIC Icu/ 53 kAIC Ics/
154 kAIC Icm @380-415V
(IEC)
15 kAIC Icu/ 7.5 kAIC Ics/
31.5 kAIC Icm @690V (IEC)
35 kAIC @600/347V (UL)
100 kAIC @240V (UL)
50 kAIC Icu/ 30 kAIC Ics/
105 kAIC Icm @480V Brazil
(IEC)

NUMBER OF POLES	Four-pole
-----------------	-----------

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

