



□□□□

Eaton

PDG34MH250P3ML

Power Defense Globally Rated, Frame 3, Four Pole, 250A-High, 65kA/480V, PXR25 LSIG w/ Modbus RTU and Relays, Std Term Load Only (PDG3X4TA401H)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG34MH250P3ML
UPC	786679345474
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.68 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING 250A High Override**VOLTAGE RATING** 600 Vac**TRIP TYPE** T293**CIRCUIT BREAKER TYPE** PD3 Global**CIRCUIT BREAKER FRAME TYPE** Complete breaker**PROTECTION** 100% neutral protection**TERMINALS** Standard Terminals Load Only**FRAME** 3**CLASS** Class A**COMMUNICATION** Modbus RTU**INTERRUPT RATING** 65 kAIC at 480 Vac**RATED OPERATION VOLTAGE (UE) AT AC - MAX** 600**VOLTAGE RATING - MAX** 600 V

INTERRUPT RATING RANGE

100 kAIC @240V (UL)
 35 kAIC @600V (UL/CSA)
 50 kAIC Icu/ 40 kAIC Ics/
 105 kAIC Icm @440V (IEC)
 65 kAIC @480V (UL)
 100 kAIC Icu/ 100 kAIC Ics/
 220 kAIC Icm @240V (IEC)
 22 kAIC Icu @250 Vdc
 15 kAIC Icu/ 7.5 kAIC Ics/
 31.5 kAIC Icm @690V (IEC)
 50 kAIC Icu/ 30 kAIC Ics/
 105 kAIC Icm @480V Brazil (IEC)
 30 kAIC Icu/ 15 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC)
 70 kAIC Icu/ 53 kAIC Ics/
 154 kAIC Icm @380-415V (IEC)

NUMBER OF POLES Four-pole (100% N)**SPECIAL FEATURES** Modbus / relays

□□

