



□□□□

Eaton PDG34N0125E4RJ

Power Defense Globally Rated, Frame 3,
Four Pole, 125A, 85kA/480V, PXR20 ARMS LSI
w/ Relays, Std Line Load Term
(PDG3X4TA300)

□□□□

| | |
|---------------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG34N0125E4RJ |
| UPC | 786679333167 |
| PRODUCT LENGTH/DEPTH | 109.1 mm |
| PRODUCT HEIGHT | 257.1 mm |
| PRODUCT WIDTH | 182.9 mm |
| PRODUCT WEIGHT | 7.68 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | CCC Marked IEC 60947-2 |



Powering Business Worldwide

□□□□

| | |
|---|-------------------------|
| AMPERAGE RATING | 125 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T284 |
| CIRCUIT BREAKER TYPE | PD3 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| PROTECTION | 100% neutral protection |
| TERMINALS | Standard Line and Load |
| FRAME | 3 |
| CLASS | Class A |
| INTERRUPT RATING | 85 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| VOLTAGE RATING - MAX | 600 V |

INTERRUPT RATING RANGE

35 kAIC Icu/ 25 kAIC Ics/
73.5 kAIC Icm @525V
South Africa (IEC)
70 kAIC Icu/ 50 kAIC Ics/
154 kAIC Icm @440V (IEC)
65 kAIC Icu/ 40 kAIC Ics/
143 kAIC Icm @480V Brazil
(IEC)
85 kAIC @480V (UL)
150 kAIC Icu/ 100 kAIC Ics/
330 kAIC Icm @240V (IEC)
70 kAIC Icu/ 70 kAIC Ics/
154 kAIC Icm @380-415V
(IEC)
20 kAIC Icu/ 10 kAIC Ics/ 42
kAIC Icm @690V (IEC)
50 kAIC @600V (UL/CSA)
150 kAIC @240V (UL)
22 kAIC Icu @250 Vdc

| | |
|-------------------------|--------------------|
| NUMBER OF POLES | Four-pole (100% N) |
| TRIP RATING | 125 A |
| SPECIAL FEATURES | Relays |

□□

