



□□□□

Eaton

PDG34N0125P2MN

Power Defense Globally Rated, Frame 3,
Four Pole, 125A, 85kA/480V, PXR25 LSI w/
Modbus RTU and Relays, No Terminals

□□□□

| | |
|---------------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG34N0125P2MN |
| UPC | 786679330630 |
| PRODUCT LENGTH/DEPTH | 109.1 mm |
| PRODUCT HEIGHT | 257.1 mm |
| PRODUCT WIDTH | 182.9 mm |
| PRODUCT WEIGHT | 7.68 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | CCC Marked IEC 60947-2 |



Powering Business Worldwide



| | |
|---|--|
| AMPERAGE RATING | 125 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T291 |
| CIRCUIT BREAKER TYPE | PD3 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| PROTECTION | 100% neutral protection |
| TERMINALS | No Terminals |
| FRAME | 3 |
| CLASS | Class A |
| COMMUNICATION | Modbus RTU |
| INTERRUPT RATING | 85 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 35 kAIC Icu/ 25 kAIC Ics/ 73.5 kAIC Icm @525V South Africa (IEC) 150 kAIC Icu/ 100 kAIC Ics/ 330 kAIC Icm @240V (IEC) 22 kAIC Icu @250 Vdc 70 kAIC Icu/ 70 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 150 kAIC @240V (UL) 20 kAIC Icu/ 10 kAIC Ics/ 42 kAIC Icm @690V (IEC) 65 kAIC Icu/ 40 kAIC Ics/ 143 kAIC Icm @480V Brazil (IEC) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @440V (IEC) 50 kAIC @600V (UL/CSA) 85 kAIC @480V (UL) |
| NUMBER OF POLES | Four-pole (100% N) |
| SPECIAL FEATURES | Modbus / relays |



