



□□□□

Eaton PDG34P0125E5XK

Power Defense Globally Rated, Frame 3, Four Pole, 125A, 100kA/480V, PXR20 ARMS LSIG w/ CAM Link, ZSI and Relays, Std Term Line Only (PDG3X4TA300)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG34P0125E5XK
UPC	786679933640
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.68 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked



Powering Business Worldwide



AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T286
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Terminals Line Only
FRAME	3
CLASS	Class A
COMMUNICATION	CAM Link
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	100 kAIC Icu/ 50 kAIC Ics/ 220 kAIC Icm @440V (IEC) 200 kAIC @240V (UL) 85 kAIC Icu/ 40 kAIC Ics/ 187 kAIC Icm @480V Brazil (IEC) 22 kAIC Icu @250 Vdc 100 kAIC Icu/ 70 kAIC Ics/ 220 kAIC Icm @380-415V (IEC) 100 kAIC @480V (UL) 20 kAIC Icu/ 10 kAIC Ics/ 42 kAIC Icm @690V (IEC) 40 kAIC Icu/ 25 kAIC Ics/ 84 kAIC Icm @525V South Africa (IEC) 65 kAIC @600V (UL/CSA) 200 kAIC Icu/ 150 kAIC Ics/ 440 kAIC Icm @240V (IEC)
NUMBER OF POLES	Four-pole (100% N)
TRIP RATING	125 A
SPECIAL FEATURES	ZSI / CAM / Relays

