



□□□□

Eaton PDG34P0600P2ML

Power Defense Globally Rated, Frame 3, Four Pole, 600A, 100kA/480V, PXR25 LSI w/ Modbus RTU and Relays, Std Term Load Only (PDG3X4TA630)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG34P0600P2ML
UPC	786689237103
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.39 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 UL 489 CCC Marked CSA



Powering Business Worldwide

□□□□

AMPERAGE RATING	600 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD3 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Terminals Load only
FRAME	3
CLASS	Class A
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

200 kAIC @240V (UL)
65 kAIC @600/347V (UL)
100 kAIC Icu/ 50 kAIC Ics/
220 kAIC Icm @440V (IEC)
85 kAIC Icu/ 40 kAIC Ics/
187 kAIC Icm @480V Brazil (IEC)
40 kAIC Icu/ 25 kAIC Ics/ 84 kAIC Icm @525V South Africa (IEC)
35 kAIC Icu/ 18 kAIC Ics/
73.5 kAIC Icm @690V (IEC)
100 kAIC @480/277V (UL)
200 kAIC Icu/ 150 kAIC Ics/
440 kAIC Icm @240V (IEC)
100 kAIC Icu/ 50 kAIC Ics/
220 kAIC Icm @380-415V (IEC)

INTERRUPT RATING RANGE	
NUMBER OF POLES	Four-pole

□□

