



□□□□

Eaton PDG43G0600TFAJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 4, Three Pole, 600A, 35kA/480V, T-M (Fxd-Adj) TU, Standard Line and Load (PDG4X3TA700)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG43G0600TFAJ
UPC	786679462607
PRODUCT LENGTH/DEPTH	111.2 mm
PRODUCT HEIGHT	406.4 mm
PRODUCT WIDTH	209.6 mm
PRODUCT WEIGHT	13.2 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CCC Marked CSA IEC 60947-2



Powering Business Worldwide

□□□□

AMPERAGE RATING	600 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T297
CIRCUIT BREAKER TYPE	PD4 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	4
CLASS	Class A
INTERRUPT RATING	35 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE

65 kAIC @240V (UL)
 18 kAIC @600V (UL/CSA)
 25 kAIC Icu/ 20 kAIC Ics/
 52.5 kAIC Icm @480V
 Brazil (IEC)
 35 kAIC @480V (UL)
 55 kAIC Icu/ 55 kAIC Ics/
 121 kAIC Icm @240V (IEC)
 36 kAIC Icu/ 36 kAIC Ics/
 75.6 kAIC Icm @380-415V
 (IEC)
 20 kAIC Icu/ 16.5 kAIC Ics/
 42 kAIC Icm @525V South
 Africa (IEC)
 22 kAIC Icu @250 Vdc
 8 kAIC Icu/ 4 kAIC Ics/ 16.8
 kAIC Icm @690V (IEC)
 30 kAIC Icu/ 22.5 kAIC Ics/
 63 kAIC Icm @440V (IEC)

NUMBER OF POLES	Three-pole
------------------------	------------

□□

