



□□□□

Eaton PDG44K0800E3MJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 4, Four Pole (100% N), 800A, 50kA/480V, PXR20 LSIG w/ Modbus RTU and Relays, Standard Line and Load (PDG4X4TA800)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG44K0800E3MJ
UPC	786679435885
PRODUCT LENGTH/DEPTH	111.2 mm
PRODUCT HEIGHT	406.4 mm
PRODUCT WIDTH	279.4 mm
PRODUCT WEIGHT	18.088 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CSA IEC 60947-2 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	800 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T285
CIRCUIT BREAKER TYPE	PD4 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Line and Load
FRAME	4
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	50 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE

35 kAIC Icu/ 35 kAIC Ics/
73.5 kAIC Icm @440V (IEC)
10 kAIC Icu/ 5 kAIC Ics/ 21
kAIC Icm @690V (IEC)
85 kAIC @240V (UL)
25 kAIC Icu/ 20 kAIC Ics/
52.5 kAIC Icm @525V
South Africa (IEC)
22 kAIC Icu @250 Vdc
35 kAIC Icu/ 22.5 kAIC Ics/
73.5 kAIC Icm @480V
Brazil (IEC)
50 kAIC @480V (UL)
85 kAIC Icu/ 85 kAIC Ics/
187 kAIC Icm @240V (IEC)
25 kAIC @600V (UL/CSA)
50 kAIC Icu/ 50 kAIC Ics/
105 kAIC Icm @380-415V
(IEC)

NUMBER OF POLES	Four-pole (100% N)
TRIP RATING	800 A
SPECIAL FEATURES	Modbus / relays

□□

