



□□□□

## Eaton PDG44K0800E5MN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 4, Four Pole (100% N), 800A, 50kA/480V, PXR20 ARMS LSIG w/ Modbus RTU and Relays, No Terminals

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG44K0800E5MN
<b>UPC</b>	786679349571
<b>PRODUCT LENGTH/DEPTH</b>	111.2 mm
<b>PRODUCT HEIGHT</b>	406.4 mm
<b>PRODUCT WIDTH</b>	279.4 mm
<b>PRODUCT WEIGHT</b>	18.088 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CCC Marked CSA IEC 60947-2 UL 489



Powering Business Worldwide



<b>AMPERAGE RATING</b>	800 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T286
<b>CIRCUIT BREAKER TYPE</b>	PD4 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>PROTECTION</b>	100% neutral protection
<b>TERMINALS</b>	No Terminals
<b>FRAME</b>	4
<b>CLASS</b>	Class A
<b>COMMUNICATION</b>	Modbus RTU
<b>INTERRUPT RATING</b>	50 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Electronic
<b>VOLTAGE RATING - MAX</b>	600 V

**INTERRUPT RATING RANGE**

85 kAIC Icu/ 85 kAIC Ics/  
187 kAIC Icm @240V (IEC)  
85 kAIC @240V (UL)  
22 kAIC Icu @250 Vdc  
50 kAIC Icu/ 50 kAIC Ics/  
105 kAIC Icm @380-415V  
(IEC)  
10 kAIC Icu/ 5 kAIC Ics/ 21  
kAIC Icm @690V (IEC)  
35 kAIC Icu/ 22.5 kAIC Ics/  
73.5 kAIC Icm @480V  
Brazil (IEC)  
25 kAIC @600V (UL/CSA)  
35 kAIC Icu/ 35 kAIC Ics/  
73.5 kAIC Icm @440V (IEC)  
25 kAIC Icu/ 20 kAIC Ics/  
52.5 kAIC Icm @525V  
South Africa (IEC)  
50 kAIC @480V (UL)

<b>NUMBER OF POLES</b>	Four-pole (100% N)
<b>TRIP RATING</b>	800 A
<b>SPECIAL FEATURES</b>	Modbus / relays



