



□□□□

Eaton PDG53K1200P5DM

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 5, Three Pole, 1200A, 50kA/480V, PXR25 ARMS LSiG w/ Modbus RTU, CAM Link and Relays, No Terminals (Metric Tapped Conductors)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG53K1200P5DM
UPC	786679746059
PRODUCT LENGTH/DEPTH	139.7 mm
PRODUCT HEIGHT	406.4 mm
PRODUCT WIDTH	209.5 mm
PRODUCT WEIGHT	21.32 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA UL 489 IEC 60947-2 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	1200 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T294
CIRCUIT BREAKER TYPE	PD5 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	5
CLASS	Class A
COMMUNICATION	Modbus RTU and CAM Link
INTERRUPT RATING	50 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	50 kAIC @480/277V (UL) 50 kAIC Icu/ 50 kAIC Ics/ 105 kAIC Icm @380-415V (IEC) 25 kAIC @600/347V (UL) 35 kAIC Icu/ 22.5 kAIC Ics/ 73.5 kAIC Icm @480V Brazil (IEC) 35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm @440V (IEC) 85 kAIC @240V (UL) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @525V South Africa (IEC) 10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC) 85 kAIC Icu/ 85 kAIC Ics/ 187 kAIC Icm @240V (IEC)
NUMBER OF POLES	Three-pole
SPECIAL FEATURES	Modbus / Relays / CAM

□□

