



□□□□

Eaton PDG54P0800E5RM

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 5, Four Pole (100% N), 800A, 100kA/480V, PXR20 ARMS LSIG w/ Relays, No Terminals (Metric Tapped Conductors)

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG54P0800E5RM |
| UPC | 786679844717 |
| PRODUCT LENGTH/DEPTH | 139.7 mm |
| PRODUCT HEIGHT | 406.4 mm |
| PRODUCT WIDTH | 282.7 mm |
| PRODUCT WEIGHT | 21.32 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | IEC 60947-2 CSA UL 489 CCC Marked |



Powering Business Worldwide



| | |
|---|---|
| AMPERAGE RATING | 800 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T286 |
| CIRCUIT BREAKER TYPE | PD5 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| PROTECTION | 100% neutral protection |
| TERMINALS | No Terminals |
| FRAME | 5 |
| CLASS | Class A |
| INTERRUPT RATING | 100 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 100 kAIC Icu/ 50 kAIC Ics/ 220 kAIC Icm @440V (IEC) 200 kAIC @240V (UL) 200 kAIC Icu/ 150 kAIC Ics/ 440 kAIC Icm @240V (IEC) 35 kAIC Icu/ 18 kAIC Ics/ 73.5 kAIC Icm @690V (IEC) 100 kAIC Icu/ 50 kAIC Ics/ 220 kAIC Icm @380-415V (IEC) 100 kAIC @480/277V (UL) 65 kAIC @600/347V (UL) 40 kAIC Icu/ 25 kAIC Ics/ 84 kAIC Icm @525V South Africa (IEC) 85 kAIC Icu/ 40 kAIC Ics/ 187 kAIC Icm @480V Brazil (IEC) |
| NUMBER OF POLES | Four-pole (100% N) |
| TRIP RATING | 800 A |
| SPECIAL FEATURES | Relays |



