



□□□□

Eaton PDG62N2500P5YN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 6, Two Pole, 2500A, 85kA/480V, PXR25 ARMS LSIG w/ Modbus RTU, CAM Link, ZSI and Relays, No Terminals

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG62N2500P5YN |
| UPC | 786679432150 |
| PRODUCT LENGTH/DEPTH | 247.7 mm |
| PRODUCT HEIGHT | 406.4 mm |
| PRODUCT WIDTH | 393.7 mm |
| PRODUCT WEIGHT | 61.23 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | CSA UL 489 CCC Marked IEC 60947-2 |



Powering Business Worldwide

□□□□

| | |
|---|--|
| AMPERAGE RATING | 2500 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T294 |
| CIRCUIT BREAKER TYPE | PD6 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| TERMINALS | No Terminals |
| FRAME | 6 |
| CLASS | Class A |
| COMMUNICATION | Modbus RTU and CAM Link |
| INTERRUPT RATING | 85 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 50 kAIC @600/347V (UL) 65 kAIC Icu/ 40 kAIC Ics/ 143 kAIC Icm @480V Brazil (IEC) 150 kAIC @240V (UL) 35 kAIC Icu/ 25 kAIC Ics/ 73.5 kAIC Icm @525V South Africa (IEC) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @440V (IEC) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 85 kAIC @480/277V (UL) 20 kAIC Icu/ 13 kAIC Ics/ 42 kAIC Icm @690V (IEC) 150 kAIC Icu/ 100 kAIC Ics/ 330 kAIC Icm @240V (IEC) |
| NUMBER OF POLES | Two-pole |
| SPECIAL FEATURES | ZSI / Modbus / Relays / CAM |

□□

