



□□□□

# Eaton

## PDG63M2500E4WN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 6, Three Pole, 2500A, 65kA/480V, PXR20 ARMS LSI w/ Modbus RTU, ZSI and Relays, No Terminals

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG63M2500E4WN
<b>UPC</b>	786679424001
<b>PRODUCT LENGTH/DEPTH</b>	247.7 mm
<b>PRODUCT HEIGHT</b>	406.4 mm
<b>PRODUCT WIDTH</b>	393.7 mm
<b>PRODUCT WEIGHT</b>	61.23 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL 489 CCC Marked IEC 60947-2 CSA



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	2500 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T284
<b>CIRCUIT BREAKER TYPE</b>	PD6 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>TERMINALS</b>	No Terminals
<b>FRAME</b>	6
<b>CLASS</b>	Class A
<b>COMMUNICATION</b>	Modbus RTU
<b>INTERRUPT RATING</b>	65 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Electronic
<b>VOLTAGE RATING - MAX</b>	600 V
<b>INTERRUPT RATING RANGE</b>	50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 65 kAIC @480/277V (UL) 30 kAIC Icu/ 25 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) 100 kAIC @240V (UL) 35 kAIC @600/347V (UL)
<b>NUMBER OF POLES</b>	Three-pole
<b>TRIP RATING</b>	2500 A
<b>SPECIAL FEATURES</b>	ZSI / Modbus / Relays

□□

