



□□□□

Eaton PDG63M2500E4XN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 6, Three Pole, 2500A, 65kA/480V, PXR20 ARMS LSI w/ CAM Link, ZSI and Relays, No Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG63M2500E4XN
UPC	786679421086
PRODUCT LENGTH/DEPTH	247.7 mm
PRODUCT HEIGHT	406.4 mm
PRODUCT WIDTH	393.7 mm
PRODUCT WEIGHT	61.23 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked CSA UL 489 IEC 60947-2



Powering Business Worldwide

□□□□

□□

AMPERAGE RATING	2500 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T284
CIRCUIT BREAKER TYPE	PD6 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	6
CLASS	Class A
COMMUNICATION	CAM Link
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC) 15 kAIC Icu/ 7.5 kAIC Ics/ 31.5 kAIC Icm @690V (IEC) 35 kAIC @600/347V (UL) 50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 30 kAIC Icu/ 25 kAIC Ics/ 63 kAIC Icm @525V South Africa (IEC) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 100 kAIC @240V (UL) 65 kAIC @480/277V (UL)
NUMBER OF POLES	Three-pole
TRIP RATING	2500 A
SPECIAL FEATURES	ZSI / CAM / Relays

