



□□□□

Eaton

PDG64N2000P2MM

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 6, Four Pole (100% N), 2000A, 85kA/480V, PXR25 LSI w/ Modbus RTU and Relays, No Terminals (Metric Tapped Conductors)

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG64N2000P2MM |
| UPC | 786687059486 |
| PRODUCT LENGTH/DEPTH | 247.7 mm |
| PRODUCT HEIGHT | 406.4 mm |
| PRODUCT WIDTH | 508 mm |
| PRODUCT WEIGHT | 52.16 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL 489 CSA IEC 60947-2 CCC Marked |



Powering Business Worldwide

□□□□

□□

| | |
|---|--|
| AMPERAGE RATING | 2000 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T291 |
| CIRCUIT BREAKER TYPE | PD6 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| PROTECTION | 100% neutral protection |
| TERMINALS | No Terminals |
| FRAME | 6 |
| CLASS | Class A |
| COMMUNICATION | Modbus RTU |
| INTERRUPT RATING | 85 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 150 kAIC @240V (UL) 150 kAIC Icu/ 100 kAIC Ics/ 330 kAIC Icm @240V (IEC) 65 kAIC Icu/ 40 kAIC Ics/ 143 kAIC Icm @480V Brazil (IEC) 85 kAIC @480/277V (UL) 20 kAIC Icu/ 13 kAIC Ics/ 42 kAIC Icm @690V (IEC) 35 kAIC Icu/ 25 kAIC Ics/ 73.5 kAIC Icm @525V South Africa (IEC) 50 kAIC @600/347V (UL) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @440V (IEC) |
| NUMBER OF POLES | Four-pole (100% N) |
| SPECIAL FEATURES | Modbus / relays |

