



Eaton PDUB151U

Eaton Tripp Lite series basic PDU, 1PH, 1U, 2 5-15P inputs, 10 ft cord, 12A, 100-125V, 6 Outlets (6) 5-15R

□□□□

PRODUCT NAME	Eaton Tripp Lite series basic PDU
CATALOG NUMBER	PDUB151U
UPC	037332253071
PRODUCT LENGTH/DEPTH	3.94 in
PRODUCT HEIGHT	1.73 in
PRODUCT WIDTH	17.24 in
PRODUCT WEIGHT	5.2 lb
WARRANTY	2 year limited
COMPLIANCES	RoHS
CERTIFICATIONS	UL 62368-1 NOM CSA Std. C22.2

FORM FACTOR	1U
PACKAGE CONTENTS	• PDUB151U 100-125V 15A Single-Phase Hot-Swap PDU • Mounting hardware • Owner's manual
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
MOUNTING DIRECTION	Horizontal
MATERIAL	Metal
INPUT CONNECTION	(2) 5-15P
CORD LENGTH	10 ft
AMPERAGE RATING	12A
ELECTRIC CURRENT - MAX	12
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
NUMBER OF OUTPUTS 5-15R	6
FEATURES	Flex Center
OUTPUT RECEPTACLES	5-15R
LED INDICATORS	Front panel LEDs report UTILITY Input Power ON (green), BYPASS-MODE Switch Setting (yellow), MASTER Outlet Power ON (green), CONTROLLABLE GROUP Outlets Power ON (green)
RECOMMENDED ELECTRICAL SERVICE	Works with most 100-125V UPS systems up to 1500VA
RECEPTACLES	5-15R
INPUT CORD LENGTH	10 ft
SWITCH CONFIGURATION	2 position Manual Transfer switch offers Break-Before-Make transfer between UPS and Utility operating modes with less than 8 milliseconds (typical) transfer time; Additional switch offers ENABLE/DISABLE control of the ECO Power-Saving feature
PRODUCT FEATURES	(2) NEMA 5-15P
CORD TYPE	Utility input cable (10 ft /

	3m) / UPS input cable (4 ft / 1.2m)
AMPERAGE RATING DETAILS	Agency de-rated to 12A continuous
OPERATING ELEVATION	0-10000 ft. (0-3000 m)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OUTPUT NOMINAL VOLTAGE	100-125V
RELATIVE HUMIDITY	5% to 95% non-condensing
FORM FACTORS SUPPORTED	Includes installation accessories for wall mount and 1U horizontal rackmount installation in 2 or 4 post equipment racks
OUTPUT CAPACITY DETAILS	1.52kW (125V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per 5-15R outlet
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	Ideal for supporting critical IT equipment that require 24/7/365 uptime 2-year limited warranty (Worldwide) Dual UPS and utility input cables with NEMA 5-15P plugs deliver AC power Transfers connected components to utility power with no downtime during UPS maintenance Mounts into 1U of rack space or onto wall using included mounting hardware ECO mode saves power by shutting down controlled outlet bank in certain conditions
PDU PLUG TYPE	5-15P
PDU TYPE	Hot-swap
PDU INPUT VOLTAGE	100 120 125
HIGH AVAILABILITY PDU FEATURES	Manual hot-swap bypass
PDU FORM FACTOR	Horizontal (1U)
TOTAL OUTLETS	6
TAA COMPLIANCE	No

