



Eaton PDUMH15AT

Eaton Tripp Lite series ATS PDU, 1PH, 1U, 2 NEMA 5-15P inputs, 12 ft cord, 1.44kW, 12A, 120V, 8 Outlets (8) 5-15R, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series ATS PDU
CATALOG NUMBER	PDUMH15AT
UPC	037332126658
PRODUCT LENGTH/DEPTH	14.5 in
PRODUCT HEIGHT	1.75 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	11 lb
WARRANTY	2 year limited
COMPLIANCES	FCC Class A RoHS
CERTIFICATIONS	NOM UL 60950-1 CSA certified



Powering Business Worldwide

FORM FACTOR

1U

PACKAGE CONTENTS

- ATS / Local Metered PDU with attached 5-15P primary input cord
- Detachable C13 to NEMA 5-15P 12 ft / 3.6m secondary input cord
- 1U rackmount installation brackets
- User manual with warranty information

OPERATING TEMPERATURE

32° to 104°F (0° to 40°C)

MOUNTING DIRECTION

Horizontal

MATERIAL

Metal

CORD LENGTH

12 ft

AMPERAGE RATING

12A

ELECTRIC CURRENT - MAX

12

PHASE

Single-phase

FREQUENCY RATING

50/60 Hz

NUMBER OF OUTPUTS 5-15R

8

FEATURES

Flex Center

FRONT PANEL LCD DISPLAY

Two digit current meter reports whole PDU output load in amps

OUTPUT RECEPTACLES

5-15R

GROUNDING OPTIONS

Rear grounding lug

LED INDICATORS

8 front panel LEDs display power on / off status for each outlet, plus 2 additional LEDs to indicate input power status for primary and secondary inputs

MINIMUM REQUIRED RACK DEPTH

17.5 in

RECOMMENDED ELECTRICAL SERVICE

Two single-phase 15A 120V circuits

RECEPTACLES

5-15R

INPUT CORD LENGTH

12 ft

TAA COMPLIANCE

Yes

PRODUCT FEATURES

TAA Compliant

CORD TYPE	Set of 2 inputs enable connection to separate PRIMARY and SECONDARY power sources
AMPERAGE RATING DETAILS	Agency de-rated to 12A continuous
OPERATING ELEVATION	0-10000 ft. (0-3000 m)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OUTPUT NOMINAL VOLTAGE	120V
RELATIVE HUMIDITY	5% to 95% non-condensing
FORM FACTORS SUPPORTED	1U rackmount
OUTPUT CAPACITY DETAILS	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 12A total capacity; 12A max per outlet
OUTPUT CAPACITY (KW)	1.44
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	Single phase 12A 120V Auto Transfer Switch / ATS PDU 1U horizontal rackmount; 2 NEMA 5-15P inputs; 8 NEMA 5-15R outlets Two digit visual current meter reports equipment load in amps; Upgrade options available Enables redundant A/B power option for single- corded network devices TAA Compliant 2-year limited warranty (Worldwide) Separate primary and secondary inputs connect to any two compatible power sources
SNMP COMPATIBILITY	Includes slot for optional SNMPWEBCARD or WEBCARDLX accessory to add built-in network interface and enable remote individual outlet control over IP
NETWORK MANAGEMENT CARDS	WEBCARDLXE SNMPWEBCARD WEBCARDLX
PDU PLUG TYPE	(2) NEMA 5-15P 5-15P
PDU TYPE	Local metered

	Auto-transfer switch
PDU INPUT VOLTAGE	120
HIGH AVAILABILITY PDU FEATURES	Auto-transfer switching
PDU FORM FACTOR	Horizontal (1U)
TOTAL OUTLETS	8
