



Eaton PDUMH20AT

Eaton Tripp Lite series ATS PDU, 1PH, 1U, 2 NEMA L5-20/5-20P inputs, 12 ft cord, 1.9kW, 16A, 120V, 16 Outlets (16) 5-20R, TAA

Specifications

PRODUCT NAME	Eaton Tripp Lite series ATS PDU
CATALOG NUMBER	PDUMH20AT
UPC	037332126665
PRODUCT LENGTH/DEPTH	14.5 in
PRODUCT HEIGHT	1.75 in
PRODUCT WIDTH	17.5 in
PRODUCT WEIGHT	12.2 lb
WARRANTY	2 year limited
COMPLIANCES	FCC Class A RoHS TAA Compliant
CERTIFICATIONS	NOM UL 60950-1 CSA certified

FORM FACTOR

1U

PACKAGE CONTENTS

- ATS / Local Metered PDU with attached L5-20P primary input cord
- Detachable C19 to NEMA L5-20P secondary input cord
- Set of two L5-20R to 5-20P plug adapters
- 1U rackmount installation brackets
- User manual with warranty information

OPERATING TEMPERATURE

32° to 104°F (0° to 40°C)

MOUNTING DIRECTION

Horizontal

MATERIAL

Metal

CORD LENGTH

12 ft

AMPERAGE RATING

16A

ELECTRIC CURRENT - MAX

16

PHASE

Single-phase

FREQUENCY RATING

50/60 Hz

NUMBER OF OUTPUTS 5-20R

16

FEATURES

Flex Center

FRONT PANEL LCD DISPLAY

Digital display reports total PDU output current in amps

OUTPUT RECEPTACLES

5-15/20R

GROUNDING OPTIONS

Rear grounding lug

LED INDICATORS

16 front panel LEDs display power on / off status for each outlet, plus 2 additional LEDs to indicate input power status for primary and secondary inputs

MINIMUM REQUIRED RACK DEPTH

19.5 in

RECOMMENDED ELECTRICAL SERVICE

Two single-phase 20A 120V circuits

RECEPTACLES

5-15/20R

INPUT CORD LENGTH	12 ft
TAA COMPLIANCE	Yes
PRODUCT FEATURES	Primary: Attached L5-20P, Secondary: C20 inlet with detachable C19-to-L5-20P cordset; L5-20-to-L5-20P adapters TAA Compliant
CORD TYPE	Set of two L5-20P cordsets with two 5-20P adapters enable connection to separate PRIMARY and SECONDARY power sources
AMPERAGE RATING DETAILS	Agency de-rated to 16A maximum
OPERATING ELEVATION	0-10000 ft. (0-3000 m)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OUTPUT NOMINAL VOLTAGE	120V
RELATIVE HUMIDITY	5% to 95% non-condensing
FORM FACTORS SUPPORTED	1U rackmount
OUTPUT CAPACITY DETAILS	1.92kW (120V) / 16A total capacity; 16A max per outlet
OUTPUT CAPACITY (KW)	1.92
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	2-year limited warranty (Worldwide) Enables redundant A/B power option for single-corded network devices Single phase 16A 120V Auto Transfer Switch / ATS PDU Two digit visual current meter reports equipment load in amps; Upgrade options available TAA Compliant Separate primary and secondary inputs connect to any two compatible power sources 1U horizontal rackmount; 2 NEMA L5-20P / 5-20P inputs; 16 5-15/20R outlets
SNMP COMPATIBILITY	Includes slot for optional SNMPWEBCARD or WEBCARDLX accessory to add built-in network

	interface and enable remote individual outlet control over IP
NETWORK MANAGEMENT CARDS	WEBCARDLXE SNMPWEBCARD WEBCARDLX
PDU PLUG TYPE	(2) NEMA 5-20P (2) NEMA L5-20P L5-20P 5-20P
PDU TYPE	Auto-transfer switch Local metered
PDU INPUT VOLTAGE	120
HIGH AVAILABILITY PDU FEATURES	Auto-transfer switching
PDU FORM FACTOR	Horizontal (1U)
TOTAL OUTLETS	16



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

