



Eaton PDUMV15

Eaton Tripp Lite series metered outlet PDU, 1PH, 0U, NEMA 5-15P input, 15 ft cord, 1.4kW, 12A, 120V, 16 Outlets (16) 5-15R

□□□□

PRODUCT NAME	Eaton Tripp Lite series local metered PDU
CATALOG NUMBER	PDUMV15
UPC	037332132536
PRODUCT LENGTH/DEPTH	1.64 in
PRODUCT HEIGHT	48.47 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	3.74 lb
WARRANTY	2 year limited
COMPLIANCES	RoHS TAA Compliant
CERTIFICATIONS	RETIE UL 60950-1 NOM

FORM FACTOR 0U (Vertical)

- PACKAGE CONTENTS**
- PDUMV15 Local Metered Vertical PDU
 - Mounting hardware and spare mounting buttons
 - Owner's manual with warranty information

OPERATING TEMPERATURE 32° to 104°F (0° to 40°C)

MOUNTING DIRECTION Vertical

MATERIAL Metal

INPUT CONNECTION NEMA 5-15P

CORD LENGTH 15 ft

AMPERAGE RATING 12A

ELECTRIC CURRENT - MAX 12

PHASE Single-phase

FREQUENCY RATING 50/60 Hz

NUMBER OF OUTPUTS 5-15R 16

FEATURES Flex Center

FRONT PANEL LCD DISPLAY Digital meter reports PDU output current in amps

OUTPUT RECEPTACLES 5-15R

OVERLOAD PROTECTION 15A circuit breaker

RECOMMENDED ELECTRICAL SERVICE Single-phase 15A 120V service

RECEPTACLES 5-15R

INPUT CORD LENGTH 15 ft

SWITCH CONFIGURATION Lighted on/off switch with transparent switch cover

TAA COMPLIANCE No

AMPERAGE RATING DETAILS Agency de-rated to 12A continuous

OPERATING ELEVATION 0-10000 ft. (0-3000 m)

OPERATING TEMPERATURE RANGE 32° to 104°F (0° to 40°C)

OUTPUT NOMINAL VOLTAGE 120V

RELATIVE HUMIDITY 5% to 95% non-condensing

FORM FACTORS SUPPORTED	Vertical (0U) mounting in rack enclosures
OUTPUT CAPACITY DETAILS	1.44kW (120V) / 12A total capacity; 12A max per outlet
OUTPUT CAPACITY (KW)	1.4
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	Toolless button mount and bolt-down bracket installation hardware included 2-year limited warranty (Worldwide) Local Metered single phase 12A 120V 0U 48in / 122cm vertical rackmount PDU 16 NEMA 5-15R outlets Attached 15-ft. (4.57 m) cord with NEMA 5-15P input plug Two-digit current meter reports output current in amps
PDU PLUG TYPE	5-15P
PDU TYPE	Local metered
PDU INPUT VOLTAGE	120
PDU FORM FACTOR	Vertical (0U)
TOTAL OUTLETS	16
