



Eaton PDUMV20

Eaton Tripp Lite series metered outlet PDU, 1PH, 0U, NEMA L5-20P/5-20P input, 15 ft cord, 1.9kW, 16A, 120V, 28 Outlets (28) 5-20R

Specifications

PRODUCT NAME	Eaton Tripp Lite series local metered PDU
CATALOG NUMBER	PDUMV20
UPC	037332132543
PRODUCT LENGTH/DEPTH	1.64 in
PRODUCT HEIGHT	60.47 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	5.39 lb
WARRANTY	2 year limited
COMPLIANCES	RoHS TAA Compliant
CERTIFICATIONS	NOM UL 60950-1 CSA Std. C22.2

FORM FACTOR

0U (Vertical)

PACKAGE CONTENTS

- PDUMV20 Local Metered Vertical PDU
- (1) L5-20P to 5-20P plug adapter
- Mounting hardware and spare mounting buttons
- Instruction manual with warranty information

OPERATING TEMPERATURE

32° to 104°F (0° to 40°C)

MOUNTING DIRECTION

Vertical

MATERIAL

Aluminum

CORD LENGTH

15 ft

AMPERAGE RATING

16A

ELECTRIC CURRENT - MAX

16

PHASE

Single-phase

FREQUENCY RATING

50/60 Hz

NUMBER OF OUTPUTS 5-20R

28

FEATURES

Flex Center

FRONT PANEL LCD DISPLAY

Digital meter reports PDU output current in amps

OUTPUT RECEPTACLES

5-15/20R

OVERLOAD PROTECTION

20A circuit breaker

RECOMMENDED ELECTRICAL SERVICE

Single-phase 20A 120V service

RECEPTACLES

5-15/20R

INPUT CORD LENGTH

15 ft

SWITCH CONFIGURATION

Lighted on/off switch with integrated transparent safety cover

TAA COMPLIANCE

No

AMPERAGE RATING DETAILS

Agency de-rated to 16A continuous

OPERATING ELEVATION

0-10000 ft. (0-3000 m)

OPERATING TEMPERATURE RANGE

32° to 104°F (0° to 40°C)

OUTPUT NOMINAL VOLTAGE

120V

RELATIVE HUMIDITY

5% to 95% non-

	condensing
FORM FACTORS SUPPORTED	Vertical
OUTPUT CAPACITY DETAILS	1.92kW (120V) / 16A total capacity; 16A max per outlet
OUTPUT CAPACITY (KW)	1.92
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	28 NEMA 5-15/20R outlets 2-year limited warranty (Worldwide) Two-digit current meter reports output current in amps Attached 15-ft. (4.57 m) cord with NEMA L5-20P plug and 5-20P adapter Local Metered single phase 120V 16A 0U 60in / 152cm vertical rackmount PDU Toolless button mount and bolt-down bracket installation hardware included
PDU PLUG TYPE	L5-20P
PDU TYPE	Local metered
PDU INPUT VOLTAGE	120
PDU FORM FACTOR	Vertical (0U)
TOTAL OUTLETS	28

□□□□:
□□□□:
□□□:
□□: