



□□□□□

Eaton PLLAW2-UNV1-M2

Eaton Crouse-Hinds series Champ Pro PLLA linear LED light fixture, Warm white, 3/4" entries, Natural alum finish, 2 ft, Glass lens, 4000 lumens, 132 lm/W, Copper-free alum, Flush ceiling mount, Wide, >0.92 PF, 120-277 Vac, 127/250 Vdc, 30W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PLLA linear LED light fixture
CATALOG NUMBER	PLLAW2-UNV1-M2
UPC	786689651060
PRODUCT LENGTH/DEPTH	25.94 in
PRODUCT HEIGHT	4.42 in
PRODUCT WIDTH	7.13 in
PRODUCT WEIGHT	15.1 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66 IP67

Product specifications

LAMP TYPE	LED
COLOR TEMPERATURE	Warm white
LAMP LENGTH	2 ft
LUMENS	4000
LUMENS PER WATT	132
OPTICAL DISTRIBUTION	Wide
MOUNTING METHOD	Flush ceiling
VOLTAGE RATING	120-277 Vac, 127/250 Vdc
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Glass
ENTRY SIZE	3/4"
FINISH	Natural aluminum
MATERIAL	Copper-free aluminum
WATTAGE	30W
POWER FACTOR	> 0.92

	IF 1941 - Champ Linear PLLA M2 LED Light Engine Fixtures
00000	IF 1938 - Champ Pro Linear PLLA M2 LED Fixtures
	IF 1948 - PLLA-M2 Linear LED with Emergency Battery Back-up
00000000	Eaton Specification Sheet - PLLAW2-UNV1-M2 Champ Pro PLLA LED Industrial Linear
	Crouse-Hinds series Global LED lighting portfolio
0000	Crouse-Hinds series industrial LED lighting solutions Crouse-Hinds series Champ PLLA LED Linear brochure
0000	Crouse-Hinds series Champ Pro PLLA LED Linear catalog page
	Champ Pro PLLA Industrial Linear LED Light Fixtures UL certification (Marine)
0000	Champ Pro PLLA Industrial Linear LED Light Fixtures UL certification Champ Pro PLLA Industrial Linear LED Light Fixtures Canadian certification

