

Eaton PV-2-25A10F85L

Eaton Bussmann series Fuse-link, high speed, 2.25 A, DC 1500 V, IEC 60269-6 type A, 10 x 85 mm, gPV, UL PV, UL, IEC

PRODUCT NAME	Eaton Bussmann series photovoltaic fuses
CATALOG NUMBER	PV-2-25A10F85L
UPC	051712698344
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	10 mm
PRODUCT WEIGHT	12 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269 UL Listed CSA Certified

AMPERAGE RATING	2.25 A
INTERRUPT RATING	30 kAIC
VOLTAGE RATING	1500 Vdc
WATT LOSSES	2.4 W

DECLARATIONS OF CONFORMITY	eaton-high-speed-photovoltaic-fuse-declaration-of-conformity-uk250925en.pdf

COLOR	White
FUSE TYPE	PV-A10F85L
MATERIAL	Fiberglass fuse

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

