



Eaton PV-2-25A14LF10F

Eaton Bussmann series Fuse-link, high speed, 2.25 A, DC 1500 V, 14 x 85 mm, gPV, IEC, UL, 10 mm fixing

□□□□

PRODUCT NAME	Eaton Bussmann series photovoltaic fuses
CATALOG NUMBER	PV-2-25A14LF10F
UPC	051712684019
PRODUCT LENGTH/DEPTH	14 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	85 mm
PRODUCT WEIGHT	20 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269 UL Listed CSA Certified

Specifications	
AMPERAGE RATING	2.25 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	1500 Vdc
WATT LOSSES	2.3 W

Declarations	
DECLARATIONS OF CONFORMITY	eaton-high-speed-photovoltaic-fuse-declaration-of-conformity-uk250926en.pdf

General	
COLOR	White
FUSE TYPE	PV-A14LF10F
MATERIAL	Ceramic

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All rights reserved.

Follow us on social media to get the latest product and support information.

