

Eaton PV-200ANH1-BC

Eaton Bussmann series Fuse-link, high speed, 200 A, DC 1000 V, NH1, gPV, UL PV, IEC, UL, dual indicator, bolted connection, M10

PRODUCT NAME	Eaton Bussmann series photovoltaic fuses
CATALOG NUMBER	PV-200ANH1-BC
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	CE
CERTIFICATIONS	IEC 60269 UL Listed CSA Certified

AMPERAGE RATING	200 A
INTERRUPT RATING	50 kAIC
VOLTAGE RATING	1000 Vdc
WATT LOSSES	25 W

DECLARATIONS OF CONFORMITY	eaton-high-speed-photovoltaic-fuse-declaration-of-conformity-uk250896en.pdf

COLOR	White
FUSE TYPE	PV-ANH1
MATERIAL	Ceramic body

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

