



## Eaton PV-25A14LF10F

Eaton Bussmann series Fuse-link, high speed, 25 A, DC 1300 V, 14 x 85 mm, gPV, IEC, UL, 10 mm fixing

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series photovoltaic fuses
<b>CATALOG NUMBER</b>	PV-25A14LF10F
<b>UPC</b>	051712377331
<b>PRODUCT LENGTH/DEPTH</b>	85 mm
<b>PRODUCT HEIGHT</b>	14 mm
<b>PRODUCT WIDTH</b>	14 mm
<b>PRODUCT WEIGHT</b>	12 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269 UL Listed CSA Certified

Specifications	
AMPERAGE RATING	25 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	1300 Vdc
WATT LOSSES	7.5 W

Declarations	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-high-speed-photovoltaic-fuse-declaration-of-conformity-uk250926en.pdf</a>

General	
COLOR	White
FUSE TYPE	PV-A14LF10F
MATERIAL	Ceramic

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All rights reserved.

Follow us on social media to get the latest product and support information.

