


## Eaton PV-350ANH3-B

Eaton Bussmann series Fuse-link, high speed, 350 A, DC 1000 V, NH3, gPV, UL PV, IEC, UL, dual indicator, bolted connection

|                             |                                          |
|-----------------------------|------------------------------------------|
|                             |                                          |
| <b>PRODUCT NAME</b>         | Eaton Bussmann series photovoltaic fuses |
| <b>CATALOG NUMBER</b>       | PV-350ANH3-B                             |
| <b>PRODUCT LENGTH/DEPTH</b> | 150 mm                                   |
| <b>PRODUCT HEIGHT</b>       | 71 mm                                    |
| <b>PRODUCT WIDTH</b>        | 71 mm                                    |
| <b>PRODUCT WEIGHT</b>       | 0.001 g                                  |
| <b>COMPLIANCES</b>          | CE Marked<br>RoHS Compliant              |
| <b>CERTIFICATIONS</b>       | IEC 60269<br>UL Listed<br>CSA Certified  |

|                  |          |
|------------------|----------|
|                  |          |
| AMPERAGE RATING  | 350 A    |
| INTERRUPT RATING | 50 kAIC  |
| VOLTAGE RATING   | 1000 Vdc |
| WATT LOSSES      | 45 W     |



|           |              |
|-----------|--------------|
|           |              |
| COLOR     | White        |
| FUSE TYPE | PV-ANH3      |
| MATERIAL  | Ceramic body |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
  
© 2025

Follow us on social media to get the latest product and support information.

