



## Eaton PV-350ANH3

Eaton Bussmann series Fuse-link, high speed, 350 A, DC 1000 V, NH3, gPV, UL PV, UL, IEC, dual indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series photovoltaic fuses
<b>CATALOG NUMBER</b>	PV-350ANH3
<b>UPC</b>	051712498111
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	32 mm
<b>PRODUCT WIDTH</b>	51 mm
<b>PRODUCT WEIGHT</b>	1110 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269 UL Listed CSA Certified

Technical Specifications	
AMPERAGE RATING	350 A
INTERRUPT RATING	50 kAIC
VOLTAGE RATING	1000 Vdc
WATT LOSSES	45 W

Compliance	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-high-speed-photovoltaic-fuse-declaration-of-conformity-uk250901en.pdf</a>

Physical Characteristics	
COLOR	White
FUSE TYPE	PV-ANH3
MATERIAL	Ceramic body

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All rights reserved.

Follow us on social media to get the latest product and support information.

