

Eaton PV-63ANH1-B

Fuse-link, high speed, 63 A, DC 1000 V, NH1, gPV, UL PV, IEC, UL, dual indicator, bolted connection

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	PV-63ANH1-B
UPC	051712531610
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	CE RoHS Compliant
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	63 A
BREAKING CAPACITY	50 kA
VOLTAGE TYPE	DC
UTILIZATION CATEGORY	gPV (photovoltaic protection)
INSULATED METAL GRIPPING LUGS (IMGL)	No
FUSE INDICATOR	Combination fuse status indicator
RATED SWITCHING CAPACITY	50 kA
FUSE SIZE	NH1
CURRENT TYPE	DC
RATED VOLTAGE DC	1000 V
CLASS	Class gPV
WATT LOSSES	12 W
FUSE SHAPE	Square body
COLOR	White
INTERRUPT RATING	50 kAIC
CONSTRUCTION SIZE	NH1
MATERIAL	Ceramic body
VOLTAGE RATING	1000 Vdc
FUSE TYPE	PV-ANH1
FITTED WITH:	Blade with bolt holes
RATED SWITCHING CAPACITY DC	50 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

